

Endress + Hauser Flowtec AG  
Kaegenstrasse 7  
4153 Reinach  
Switzerland

Our reference  
CBA/301110528D

Contact person  
Ir J.P.H. Wuister

Your reference  
-

Subject  
Bestätigung

Date  
November 16th, 2001


### **Bestätigung**

Ein Druckgerät, welches an die Rohrleitung angeflanscht, eingeschweisst oder eingeschraubt wird und kein eigenes identifizierbares druckbeaufschlagtes Gehäuse hat, unterliegt, unabhängig vom zulässigen Prozessdruck, nicht der Druckgeräterichtlinie 97/23/EG (Art. 1, 2.1.4).  
Dies betrifft die folgenden Durchflussmesser von Endress + Hauser Flowtec AG:

Magnetisch induktive Durchflussmesser:  
Magphant

Ultraschall Durchflussmesser:  
Prosonic Flow 9\*W-B\*\*\*\*\*  
Prosonic Flow DK9WF-K mit Sensorhalter DK9SH-C/D/E/F  
DDU15S  
DDU15D

Unterscrieben im Namen Stoomwezen BV



Ir. J.P.H. Wuister  
Consultant CE-marking

Endress + Hauser Flowtec AG  
Kaegenstrasse 7  
4153 Reinach  
Switzerland

Our reference  
CBA/301110528

Contact person  
Ir J.P.H. Wuister

Your reference  
-

Subject  
Confirmation

Date  
November 16th, 2001

We confirm the following:

A pressure equipment which is intended to be flanged, welded or threaded to a pipe and having no identifiable pressure compartment is not subject of the Pressure Equipment Directive 97/23/EC (Art. 1, 2.1.4) independent of the maximum allowable amount of pressure.

This applies to the following flowmeters of Endress + Hauser Flowtec AG:

Electromagnetic flowmeters:  
Magphant

Ultrasonic flowmeters:  
Prosonic Flow 9\*W-B\*\*\*\*\*  
Prosonic Flow DK9WF-K with sensor holder DK9SH-C/D/E/F  
DDU15S  
DDU15D

Signed on behalf of Stoomwezen BV



Ir. J.P.H. Wuister  
Consultant CE-marking